

KIR-Rohre					P	K	WS	Material	
	KIR-Rohr ØI 17.2	-20	1005	10	31.85	19.65	21.—	P	1.30
				20	43.15	26.60	28.—	K	—.95
				24	24.70	15.30	16.—		
	ØI 21.5	25	1006	10	32.45	20.15	21.—	P	1.95
				20	43.75	27.05	29.—	K	1.45
				24	25.30	15.75	16.—		
	ØI 28.2	32	1007	10	33.45	20.85	22.—	P	2.95
				20	44.75	27.80	29.—	K	2.20
				24	26.30	16.50	17.—		
	ØI 35.8	40	1008	10	44.80	28.—	29.—	P	4.45
				20	61.20	38.05	40.—	K	3.30
				24	31.25	19.70	20.—		
KIR-Rohre hf lichtgr									
	KIR-Rohr hf lichtgr ØI 17.0	-20	125 140	10	33.40	20.85	22.—	P	2.90
				20	44.70	27.75	29.—	K	2.15
				24	26.25	16.45	17.—		
	ØI 21.6	25	125 141	10	34.30	21.45	22.—	P	3.75
				20	45.60	28.40	30.—	K	2.75
				24	27.10	17.10	18.—		
	ØI 27.7	32	125 142	10	36.85	23.35	24.—	P	6.30
				20	48.15	30.25	31.—	K	4.65
				24	29.65	18.95	19.—		
	ØI 35.5	40	125 143	10	48.85	31.—	32.—	P	8.50
				20	65.25	41.—	42.—	K	6.30
				24	35.25	22.65	23.—		
KIR-Bögen									
	KIR-Bogen steckbar	-20	1138	24	26.95	16.75	18.—	P	1.90
								K	1.40
		25	1139	24	27.60	17.20	18.—	P	2.55
								K	1.85
		32	1140	24	28.45	17.85	18.—	P	3.40
								K	2.50
	KIR-Bogen -25 m Biegefeder erstellen	45-90°	1018	09	30.70	18.80	20.—		
KRH-Rohre									
	KRH-Rohr ØI 15.8	20	1031	10	33.20	20.65	22.—	P	2.70
				20	44.50	27.60	29.—	K	2.—
				24	26.05	16.30	17.—		
	ØI 20.6	25	1032	10	34.35	21.55	22.—	P	3.85
				20	45.65	28.45	30.—	K	2.85
				24	27.20	17.15	18.—		
	ØI 27	32	1033	10	36.40	23.—	24.—	P	5.85
				20	47.70	29.95	31.—	K	4.30
				24	29.20	18.65	19.—		
	ØI 34	40	1034	10	49.20	31.25	32.—	P	8.85
				20	65.60	41.30	43.—	K	6.55
				24	35.60	22.95	23.—		
	KRH-Bogen m Fön erstellen	45-90°	1028	09	33.90	20.75	22.—		
Rohrschellen Clic									
	Rohrschelle Clic	-20	126 274	10	9.20	5.75	6.—	P	—.90
				20	13.90	8.65	9.—	K	—.65
		25	126 275	10	9.55	6.—	6.—	P	1.25
				20	14.25	8.90	9.50	K	—.90
		32	126 276	10	9.75	6.15	6.50	P	1.45
				20	14.45	9.—	9.50	K	1.05
		40	126 277	10	10.25	6.55	6.50	P	2.—
				20	15.—	9.40	9.50	K	1.45